


GWA30

Shaft block

Technical information



Your current product variant

Size code 30

Main Dimensions & Performance Data

D	30 mm	Diameter
B	84 mm	Width
L	28 mm	Length
H	68 mm	Height
≈m	0,38 kg	Weight

Mounting dimensions

J B	68 mm	Mounting Dimension
Tol J B	+ 0,2 mm	Upper tolerance
Tol J B	- 0,2 mm	Lower tolerance
B 1	45 mm	Mounting Dimension
H 2	40 mm	Mounting Dimension
Tol H 2	+ 0,15 mm	Upper tolerance
Tol H 2	- 0,15 mm	Lower Tolerance
H 8	9,5 mm	Mounting Dimension
N 1	9 mm	Mounting Dimension
N 3	18 mm	Mounting Dimension
K 5	M8	Size thread fixing screws above
W	5 mm	Width across flats