




PHE30-XL

Take-up housing unit

Take-up housing units PHE, cast iron housing, radial insert ball bearing with eccentric locking collar, P seals

X-life

Technical information



Your current product variant

Material	GG	Grey cast iron
----------	----	----------------

Main Dimensions & Performance Data

d	30 mm	Bore diameter
L	114 mm	Length total
M	85 mm	Housing total width
A 2	32 mm	Width housing
≈m	1,12 kg	Weight

Mounting dimensions

K	M24	Thread fixing bore
K 1	24 mm	Thread depth

Dimensions

L 1	72 mm	Distance shaft axis
T	40 mm	Height housing fixing side
W 2	40 mm	Length of guidance face
Q	M6	Connection thread for lubrication



Additional information

HE06	Housing
GRAE30-XL-NPP-B	Bearing designation

Temperature range

T _{min}	-20 °C	Operating temperature min.
T _{max}	120 °C	Operating temperature max.