



AXW15

Axial needle roller bearing



Axial needle roller bearings, single direction,
AXK with axial bearing washer

Technical information



Main Dimensions & Performance Data

D _{c1}	15 mm	Bore diameter cage
D	31 mm	Outside diameter bearing washer
B	3,2 mm	Height bearing
B ₁	3,5 mm	Height centering collar
D ₁	21 mm	Outside diameter centering collar
E _a	27 mm	Raceway dimension
E _b	17 mm	Raceway dimension
C	11.400 N	Basic dynamic load rating, axial
C _{0a}	36.000 N	Basic static load rating, axial
c _{ua}	3.650 N	Fatigue load limit, axial
n _G	13.400 1/min	Limiting speed
n _{gr}	6.400 1/min	Reference speed
≈m	10,5 g	Weight



Additional information

AS1528	Axial bearing washer
HK1514-RS	Drawn cup needle roller bearings turned
HK1516	Drawn cup needle roller bearings
HK1522-ZW	Drawn cup needle roller bearings
HK1512	Drawn cup needle roller bearings for radial bearing arrangement
BK1512	Needle bush
BK1516	Needle bush

Characteristics

-  Axial load in one direction
-  Grease Lubrication
-  Oil Lubrication
-  Not sealed
-  Small design envelope