


**205-XL-KRR**

Deep groove ball bearing

Radial insert ball bearings 2..-KRR, cylindrical outer ring, inner ring for fit, R seals on both sides

X-life

Technical information

**Your current product variant**

Sealing	KRR	Lip seals on both sides
---------	-----	-------------------------

Main Dimensions & Performance Data

d	25 mm	Bore diameter
D	52 mm	Outside diameter
B	21 mm	Width
C _r	14.900 N	Basic dynamic load rating, radial
C _{0r}	7.800 N	Basic static load rating, radial
m	0,158 kg	Weight

Dimensions

D ₁	42,6 mm	Outside diameter seal
C	15 mm	Width, outer ring
C ₂	17,4 mm	Sealing total width
d ₁	33,8 mm	Rib diameter inner ring
r _{min}	1 mm	Minimum chamfer dimension

Temperature range

T _{min}	-20 °C	Operating temperature min.
T _{max}	100 °C	Operating temperature max.



Calculation factors

f_0	13,8	Calculation factor
-------	------	--------------------

Characteristics

-  Radial load
-  Axial load in one direction
-  Axial load in two directions
-  Lifetime lubrication, freedom from maintenance
-  Grease Lubrication
-  Sealed on both sides