



**3004-2RS-C3**

Angular contact ball bearing

Angular contact ball bearing 30...-B-2RS-TVH,
double row, seals, plastic cage

Technical information



Your current product variant

Design variant	B	Bearing without filling slot
Sealing	2RS	Contact seal on both sides
Cage	TVH	Solid cage made of glass-fiber reinforced polyamide PA66
Tolerance class	PN	Normal (ISO 492:2023)
Dimensional / heat stabilization	SN	Rings dimensional stabilized up to 120°
Lubricant	GA14	Ball bearing grease, low noise
Axial internal clearance	C3	Group 3 (C3), bigger than CN

Main Dimensions & Performance Data

d	20 mm	Bore diameter
D	42 mm	Outside diameter
B	16 mm	Width
C _r	14.300 N	Basic dynamic load rating, radial
C _{0r}	9.400 N	Basic static load rating, radial
C _{ur}	490 N	Fatigue load limit, radial
n _G	10.500 1/min	Limiting speed
m	0,091 kg	Weight



Mounting dimensions

$d_{a \min}$	23,2 mm	Minimum diameter shaft shoulder
$D_{a \max}$	38,8 mm	Maximum diameter of housing shoulder
$r_{a \max}$	0,6 mm	Maximum fillet radius

Dimensions

$r_{\min}$	0,6 mm	Minimum chamfer dimension
D_1	35 mm	Shoulder diameter outer ring
D_2	36,38 mm	Caliber diameter outer ring
d_1	27,1 mm	Shoulder diameter inner ring
d_2	25,31 mm	Caliber diameter inner ring
a	21,1 mm	Distance between the apexes of the pressure cones
α	25 °	Contact angle

Temperature range

$T_{\min}$	-20 °C	Operating temperature min.
$T_{\max}$	100 °C	Operating temperature max.

Characteristics

	Radial load
	Axial load in one direction
	Axial load in two directions
	Lifetime lubrication, freedom from maintenance
	Grease Lubrication
	Sealed on both sides