



**3000-2Z**

Angular contact ball bearing

Angular contact ball bearing 30...-B-2RZ-TVH,
double row, shields, plastic cage

Technical information



Ihre aktuelle Produktvariante

Design variant	B	Bearing without filling slot
Type of Seal	2RZ	Non-contact seal on both sides
Cage	TVH	Solid cage made of glass-fiber reinforced polyamide PA66
Tolerance class	PN	Normal (ISO 492:2023)
Dimensional / heat stabilization	SN	Rings dimensional stabilized up to 120°
Lubricant	GA13	Ball bearing and insert bearing grease
Axial internal clearance	CN	Group N (CN)

Main Dimensions & Performance Data

d	10 mm	Bore diameter
D	26 mm	Outside diameter
B	12 mm	Width
C _r	5.700 N	Basic dynamic load rating, radial
C _{0r}	3.200 N	Basic static load rating, radial
C _{ur}	166 N	Fatigue load limit, radial
n _G	23.400 1/min	Limiting speed
n _{gr}	21.900 1/min	Reference speed
≈m	0,03 kg	Gewicht



Mounting dimensions

$d_{a \min}$	12 mm	Minimum diameter shaft shoulder
$D_{a \max}$	24 mm	Maximum diameter of housing shoulder
$r_{a \max}$	0,3 mm	Maximum fillet radius

Dimensions

$r_{\min}$	0,3 mm	Minimum chamfer dimension
D_1	20,65 mm	Shoulder diameter outer ring
D_2	21,16 mm	Caliber diameter outer ring
d_1	15,6 mm	Shoulder diameter inner ring
d_2	14,25 mm	Caliber diameter inner ring
a	12,6 mm	Distance between the apexes of the pressure cones
α	25 °	Contact angle

Temperature range

$T_{\min}$	-20 °C	Operating temperature min.
$T_{\max}$	120 °C	Operating temperature max.

Eigenschaften

	Radiale Last
	Axiale Last aus einer Richtung
	Axiale Last aus zwei Richtungen
	Lebensdauerschmierung, Wartungsfreiheit
	Fettschmierung
	Beidseitig abgedichtet