



**FAG****X-life****3213-BD-XL-2HRS-TVH-C3**

Angular contact ball bearing

Angular contact ball bearing 32..-BD-XL-2HRS-TVH, double row, X-life, seals, plastic cage

Technical information



Your current product variant

Design variant	B	Bearing without filling slot
Changed internal design	D	D
Type of Seal	2HRS	Contact seal on both sides
Cage	TVH	Solid cage made of glass-fiber reinforced polyamide PA66
Tolerance class	P6	Class 6 (ISO 492:2023)
Dimensional / heat stabilization	S0	Rings dimensional stabilized up to 150°
Lubricant	GA13	Ball bearing and insert bearing grease
Axial internal clearance	C3	Group 3 (C3), bigger than CN

Main Dimensions & Performance Data

d	65 mm	Bore diameter
D	120 mm	Outside diameter
B	38,1 mm	Width
C _r	86.000 N	Basic dynamic load rating, radial
C _{0r}	77.000 N	Basic static load rating, radial
C _{ur}	5.300 N	Fatigue load limit, radial
n _G	4.300 1/min	Limiting speed
≈m	1,63 kg	Weight



Mounting dimensions

$d_{a \min}$	74 mm	Minimum diameter shaft shoulder
$D_{a \max}$	111 mm	Maximum diameter of housing shoulder
$r_{a \max}$	1,5 mm	Maximum fillet radius

Dimensions

$r_{\min}$	1,5 mm	Minimum chamfer dimension
D_1	106,64 mm	Shoulder diameter outer ring
D_2	110,13 mm	Caliber diameter outer ring
d_1	87,7 mm	Shoulder diameter inner ring
d_2	85,28 mm	Caliber diameter inner ring
a	70,6 mm	Distance between the apexes of the pressure cones
α	30 °	Contact angle

Temperature range

$T_{\min}$	-20 °C	Operating temperature min.
$T_{\max}$	100 °C	Operating temperature max.

Characteristics

	Radial load
	Axial load in one direction
	Axial load in two directions
	Lifetime lubrication, freedom from maintenance
	Grease Lubrication
	Sealed on both sides