



**FAG****X-life****3304-BD-XL-2HRS-TVH**

Angular contact ball bearing

Angular contact ball bearing 33..-BD-XL-2HRS-TVH, double row, X-life, seals, plastic cage

Technical information



Your current product variant

Design variant	B	Bearing without filling slot
Changed internal design	D	D
Type of Seal	2HRS	Contact seal on both sides
Cage	TVH	Solid cage made of glass-fiber reinforced polyamide PA66
Tolerance class	P6	Class 6 (ISO 492:2023)
Dimensional / heat stabilization	SN	Rings dimensional stabilized up to 120°
Lubricant	GA13	Ball bearing and insert bearing grease
Axial internal clearance	CN	Group N (CN)

Main Dimensions & Performance Data

d	20 mm	Bore diameter
D	52 mm	Outside diameter
B	22,2 mm	Width
C _r	24.600 N	Basic dynamic load rating, radial
C _{0r}	15.900 N	Basic static load rating, radial
C _{ur}	1.100 N	Fatigue load limit, radial
n _G	11.000 1/min	Limiting speed
≈m	0,21 kg	Weight



Mounting dimensions

$d_{a\ min}$	27 mm	Minimum diameter shaft shoulder
$D_{a\ max}$	45 mm	Maximum diameter of housing shoulder
$r_{a\ max}$	1 mm	Maximum fillet radius

Dimensions

$r_{\min}$	1,1 mm	Minimum chamfer dimension
D_1	43,98 mm	Shoulder diameter outer ring
D_2	46,14 mm	Caliber diameter outer ring
d_1	33,52 mm	Shoulder diameter inner ring
d_2	31,94 mm	Caliber diamter inner ring
a	30,4 mm	Distance between the apexes of the pressure cones
α	30 °	Contact angle

Temperature range

$T_{\min}$	-20 °C	Operating temperature min.
$T_{\max}$	100 °C	Operating temperature max.

Characteristics

	Radial load
	Axial load in one direction
	Axial load in two directions
	Lifetime lubrication, freedom from maintenance
	Grease Lubrication
	Sealed on both sides