



**81136-M**

Axial cylindrical roller bearing

Axial cylindrical roller bearing 811...-M, single row

Technical information



Your current product variant

Cage	M	Brass Cage
------	---	------------

Main Dimensions & Performance Data

d	180 mm	Bore diameter
T	34 mm	Height
C _a	340.000 N	Basic dynamic load rating, axial
C _{0a}	1.300.000 N	Basic static load rating, axial
C _{ua}	116.000 N	Fatigue load limit, axial
n _G	1.420 1/min	Limiting speed
n _{gr}	580 1/min	Reference speed
D	225 mm	Outside diameter
m	3,194 kg	Weight

Mounting dimensions

d _{a min}	219 mm	Minimum diameter shaft shoulder
D _{a max}	185 mm	Maximum diameter of housing shoulder
r _{a max}	1,1 mm	Maximum recess radius



Dimensions

D ₁	183 mm	Bore diameter housing washer
d ₁	222 mm	Rip diameter shaft washer
r _{min}	1,1 mm	Minimum chamfer dimension

Temperature range

T _{min}	-30 °C	Operating temperature min.
T _{max}	120 °C	Operating temperature max.

Additional information

K81136-M	Axial roller and cage assembly
GS81136	Housing Washer
WS81136	Shaft washer

Characteristics

	Axial load in one direction
	Grease Lubrication
	Oil Lubrication
	Not sealed