



**81113-TV** **Axial cylindrical roller bearing**

Axial cylindrical roller bearings 811, single direction, comprising K811, GS, WS

Technical information**Your current product variant**

Cage	TV	Plastic Cage made from PA66
------	----	-----------------------------

Main Dimensions & Performance Data

d	65 mm	Bore diameter
T	18 mm	Height
C _a	107.000 N	Basic dynamic load rating, axial
C _{0a}	340.000 N	Basic static load rating, axial
C _{ua}	34.500 N	Fatigue load limit, axial
n _G	3.700 1/min	Limiting speed
n _{gr}	1.260 1/min	Reference speed
D	90 mm	Outside diameter
m	311,56 g	Weight

Mounting dimensions

d _{a min}	87 mm	Minimum diameter shaft shoulder
D _{a max}	67 mm	Maximum diameter of housing shoulder
r _{a max}	1 mm	Maximum recess radius



Dimensions

D ₁	67 mm	Bore diameter housing washer
d ₁	90 mm	Rip diameter shaft washer
r _{min}	1 mm	Minimum chamfer dimension

Temperature range

T _{min}	-30 °C	Operating temperature min.
T _{max}	120 °C	Operating temperature max.

Additional information

K81113-TV	Axial roller and cage assembly
GS81113	Housing Washer
WS81113	Shaft washer
LS6590	Track Washer

Characteristics

	Axial load in one direction
	Grease Lubrication
	Oil Lubrication
	Not sealed