



**81116-TV** **Axial cylindrical roller bearing**

Axial cylindrical roller bearings 811, single direction, comprising K811, GS, WS

Technical information**Your current product variant**

Cage	TV	Plastic Cage made from PA66
------	----	-----------------------------

Main Dimensions & Performance Data

d	80 mm	Bore diameter
T	19 mm	Height
C _a	106.000 N	Basic dynamic load rating, axial
C _{0a}	350.000 N	Basic static load rating, axial
C _{ua}	36.000 N	Fatigue load limit, axial
n _G	3.100 1/min	Limiting speed
n _{gr}	1.170 1/min	Reference speed
D	105 mm	Outside diameter
m	386,4 g	Weight

Mounting dimensions

d _{a min}	102 mm	Minimum diameter shaft shoulder
D _{a max}	83 mm	Maximum diameter of housing shoulder
r _{a max}	1 mm	Maximum recess radius



Dimensions

D ₁	82 mm	Bore diameter housing washer
d ₁	105 mm	Rip diameter shaft washer
r _{min}	1 mm	Minimum chamfer dimension

Temperature range

T _{min}	-30 °C	Operating temperature min.
T _{max}	120 °C	Operating temperature max.

Additional information

K81116-TV	Axial roller and cage assembly
GS81116	Housing Washer
WS81116	Shaft washer
LS80105	Track Washer

Characteristics

 F _a	Axial load in one direction
	Grease Lubrication
	Oil Lubrication
	Not sealed