



**FAG****29440-E1-XL**

Axial spherical roller bearing

Axial spherical roller bearing 294...E1-XL, no flanging ring

**X-life**

Technical information



Your current product variant

Heat treatment	Standard	Standard
Locating feature, housing washer	Without	
Cage	JP	Sheet metal cage
Handling thread holes	Without	
Constricted width and inclination variation	Standard	
Test certificate	Without	

Main Dimensions & Performance Data

d	200 mm	Bore diameter
D	400 mm	Outside diameter
T	122 mm	Height
C _a	3.450.000 N	Basic dynamic load rating, axial
C _{0a}	9.500.000 N	Basic static load rating, axial
C _{ua}	950.000 N	Fatigue load limit, axial
n _G	1.670 1/min	Limiting speed
n _{gr}	860 1/min	Reference speed
≈m	66,06 kg	Weight



Mounting dimensions

d _{a min}	295 mm	Minimum diameter shaft shoulder
D _{a max}	338 mm	Maximum diameter of housing shoulder
D _{b min}	406 mm	Minimum bore diameter housing
d _{b max}	234 mm	Maximum distance sleeve
d _{b1 max}	220 mm	Maximum chamfer diameter of distance sleeve
r _{a max}	4 mm	Maximum recess radius
	30 °	Angle of chamfer of the distance sleeve

Dimensions

D ₁	277,5 mm	Bore diameter housing washer
d ₁	360 mm	Rip diameter shaft washer
r _{min}	5 mm	Minimum chamfer dimension
T ₁	59,4 mm	Height of the housing washer
T ₃	77 mm	Height of the shaft washer
T ₅	106,9 mm	Distance shaft washer - cage
A	122 mm	Distance of the center point

Temperature range

T _{min}	-30 °C	Operating temperature min.
T _{max}	200 °C	Operating temperature max.



Characteristics

-  Radial load
-  Axial load in one direction
-  Grease Lubrication
-  Oil Lubrication
-  Not sealed
-  Large bearing
-  Static angular error and misalignment
-  Dynamic angular error and misalignment