



**RRY30-VA** **Flanged housing unit**

Housing units RRY..-VA, three/four-bolt flanged housing units, sheet steel, grub screws in inner ring, R seals, with anti-corrosion protection, without relubrication facility

Technical information**Your current product variant**

Material	VA	Stainless Steel
Special material	VA	Corrosion-resistant VA design

Main Dimensions & Performance Data

d	30 mm	Bore diameter
H	112,7 mm	Height flange
U	24,7 mm	Total height unit
C _r	18.700 N	Basic dynamic load rating, radial
C _{0r}	10.700 N	Basic static load rating, radial
C _{ur}	530 N	Fatigue load limit, radial
C _{0r G}	5.000 N	Load carrying capacity (housing)
≈m	0,6 kg	Weight

Mounting dimensions

J	90,5 mm	Pitch circle diameter (holes)
N	10,5 mm	Fixing square
n	3	Number of screwing holes



Dimensions

A	9 mm	Height housing
B	38,1 mm	Width
S	2,5 mm	Thickness of flange
V	71 mm	Shoulder diameter housing

Additional information

2	Number of housings
FLAN62-MSB-VA	Housing
GYE30-KRR-B-VA	Bearing designation

Temperature range

T _{min}	-35 °C	Operating temperature min.
T _{max}	100 °C	Operating temperature max.