

**KN12-B-PP** **Linear Ball Bearing**

Linear ball bearings KN...-B-PP, Lightweight range, closed design, sealed on all sides, with relubrication facility, adjustable angle

Technical information**Your current product variant**

Size code	12	
Seal	PP	Sealed

Main Dimensions & Performance Data

F_w	12 mm	Bore diameter
D	22 mm	Outside diameter
L	32 mm	Length
C_{min}	730 N	Load capacity dyn.
$C_{0 min}$	510 N	Load capacity stat.
C_{max}	870 N	Load capacity dyn.
$C_{0 max}$	740 N	Load capacity stat.
$\approx m$	20 g	Weight

Mounting dimensions

L_2	22,6 mm
B_{L2}	1,3 mm
D_N	21 mm
T_4	0,7 mm
N_4	3 mm
$b_{1 max}$	1,5 mm

5

Number of rows balls