

**KN20-B-PP** **Linear Ball Bearing**

Linear ball bearings KN...-B-PP, Lightweight range, closed design, sealed on all sides, with relubrication facility, adjustable angle

Technical information**Your current product variant**

Size code	20	
Seal	PP	Sealed

Main Dimensions & Performance Data

F_w	20 mm	Bore diameter
D	32 mm	Outside diameter
L	45 mm	Length
C_{min}	1.730 N	Load capacity dyn.
$C_{0 min}$	1.230 N	Load capacity stat.
C_{max}	1.830 N	Load capacity dyn.
$C_{0 max}$	1.570 N	Load capacity stat.
$\approx m$	60 g	Weight

Mounting dimensions

L_2	31,2 mm
B_{L2}	1,6 mm
D_N	30,7 mm
T_4	0,9 mm
N_4	3 mm
$b_{1 max}$	2,5 mm

6

Number of rows balls