

**KN25-B-PP** **Linear Ball Bearing**

Linear ball bearings KN...-B-PP, Lightweight range, closed design, sealed on all sides, with relubrication facility, adjustable angle

Technical information**Your current product variant**

Size code	25	
Seal	PP	Sealed

Main Dimensions & Performance Data

F_w	25 mm	Bore diameter
D	40 mm	Outside diameter
L	58 mm	Length
C_{min}	3.100 N	Load capacity dyn.
$C_{0 min}$	2.220 N	Load capacity stat.
C_{max}	3.250 N	Load capacity dyn.
$C_{0 max}$	2.850 N	Load capacity stat.
$\approx m$	0,135 kg	Weight

Mounting dimensions

L_2	43,7 mm
B_{L2}	1,85 mm
D_N	38,5 mm
T_4	1,4 mm
N_4	3 mm
$b_{1 max}$	2,5 mm

6

Number of rows balls