

**KNO30-B-PP** **Linear Ball Bearing**

Linear ball bearings KNO...-B-PP, Lightweight range, open design, sealed on all sides, with relubrication facility, adjustable angle

Technical information**Your current product variant**

Size code	30	
Seal	PP	Sealed

Main Dimensions & Performance Data

F _w	30 mm	Bore diameter
D	47 mm	Outside diameter
L	68 mm	Length
C _{max}	3.750 N	Load capacity dyn.
C _{0 max}	2.850 N	Load capacity stat.
≈m	0,161 kg	Weight

Mounting dimensions

B ₂	14 mm	Width of sector opening
T ₄	2,2 mm	
A ₁₀	2 mm	Angle of sector opening
N ₄	3 mm	
α	57 °	Angle of sector opening
b _{1 max}	2,5 mm	
	5	Number of rows balls

