

**KH08-PP** **Linear Ball Bearing**

Linear ball bearings with initial greasing,
sealed on both sides, with relubrication facility

Technical information**Your current product variant**

Size code	08	
Seal	PP	Sealed

Main Dimensions & Performance Data

F_w	8 mm	Diameter shaft
D	15 mm	Outer diameter
L	24 mm	Length
C_{min}	410 N	Load capacity dyn.
$C_{0 min}$	280 N	Load capacity stat.
C_{max}	475 N	Load capacity dyn.
$C_{0 max}$	400 N	Load capacity stat.
$\approx m$	12,05 g	Weight

Mounting dimensions

J_{L4}	6 mm
N_2	2 mm

