



KH10-PP [↗](#)

Linear Ball Bearing

Linear ball bearings with initial greasing,
sealed on both sides, with relubrication facility

Technical information

Your current product variant

Size code	10	
Seal	PP	Sealed

Main Dimensions & Performance Data

F_w	10 mm	Diameter shaft
D	17 mm	Outer diameter
L	26 mm	Length
C_{min}	510 N	Load capacity dyn.
$C_{0 min}$	370 N	Load capacity stat.
C_{max}	590 N	Load capacity dyn.
$C_{0 max}$	520 N	Load capacity stat.
$\approx m$	14,95 g	Weight

Mounting dimensions

J_{L4}	6 mm
N_2	2,5 mm

