



KH12-PP [↗](#)

Linear Ball Bearing

Linear ball bearings with initial greasing,
sealed on both sides, with relubrication facility

Technical information

Your current product variant

Size code	12	
Seal	PP	Sealed

Main Dimensions & Performance Data

F_w	12 mm	Diameter shaft
D	19 mm	Outer diameter
L	28 mm	Length
C_{min}	670 N	Load capacity dyn.
$C_{0 min}$	510 N	Load capacity stat.
C_{max}	800 N	Load capacity dyn.
$C_{0 max}$	740 N	Load capacity stat.
$\approx m$	18,85 g	Weight

Mounting dimensions

J_{L4}	6 mm
N_2	2,5 mm

