

**KH14-PP** **Linear Ball Bearing**

Linear ball bearings with initial greasing,
sealed on both sides, with relubrication facility

Technical information**Your current product variant**

Size code	14	
Seal	PP	Sealed

Main Dimensions & Performance Data

F_w	14 mm	Diameter shaft
D	21 mm	Outer diameter
L	28 mm	Length
C_{min}	690 N	Load capacity dyn.
$C_{0 min}$	520 N	Load capacity stat.
C_{max}	830 N	Load capacity dyn.
$C_{0 max}$	760 N	Load capacity stat.
$\approx m$	20,355 g	Weight

Mounting dimensions

J_{L4}	6 mm
N_2	2,5 mm

