



KH16-PP [↗](#)

Linear Ball Bearing

Linear ball bearings with initial greasing,
sealed on both sides, with relubrication facility

Technical information

Your current product variant

Size code	16	
Seal	PP	Sealed

Main Dimensions & Performance Data

F_w	16 mm	Diameter shaft
D	24 mm	Outer diameter
L	30 mm	Length
C_{min}	890 N	Load capacity dyn.
$C_{0 min}$	620 N	Load capacity stat.
C_{max}	1.060 N	Load capacity dyn.
$C_{0 max}$	910 N	Load capacity stat.
$\approx m$	27,275 g	Weight

Mounting dimensions

J_{L4}	7 mm
N_2	2,5 mm

