



KH20-PP [↗](#)

Linear Ball Bearing

Linear ball bearings with initial greasing,
sealed on both sides, with relubrication facility

Technical information

Your current product variant

Size code	20	
Seal	PP	Sealed

Main Dimensions & Performance Data

F_w	20 mm	Diameter shaft
D	28 mm	Outer diameter
L	30 mm	Length
C_{min}	1.110 N	Load capacity dyn.
$C_{0 min}$	790 N	Load capacity stat.
C_{max}	1.170 N	Load capacity dyn.
$C_{0 max}$	1.010 N	Load capacity stat.
$\approx m$	32,65 g	Weight

Mounting dimensions

J_{L4}	7 mm
N_2	2,5 mm

