

**KH25-PP** **Linear Ball Bearing**

Linear ball bearings with initial greasing,
sealed on both sides, with relubrication facility

Technical information**Your current product variant**

Size code	25	
Seal	PP	Sealed

Main Dimensions & Performance Data

F_w	25 mm	Diameter shaft
D	35 mm	Outer diameter
L	40 mm	Length
C_{min}	2.280 N	Load capacity dyn.
$C_{0 min}$	1.670 N	Load capacity stat.
C_{max}	2.420 N	Load capacity dyn.
$C_{0 max}$	2.130 N	Load capacity stat.
$\approx m$	65,6 g	Weight

Mounting dimensions

J_{L4}	8 mm
N_2	2,5 mm

