



KH40-PP [↗](#)

Linear Ball Bearing

Linear ball bearings with initial greasing,
sealed on both sides, with relubrication facility

Technical information

Your current product variant

Size code	40	
Seal	PP	Sealed

Main Dimensions & Performance Data

F_w	40 mm	Diameter shaft
D	52 mm	Outer diameter
L	60 mm	Length
C_{min}	5.300 N	Load capacity dyn.
$C_{0 min}$	4.450 N	Load capacity stat.
C_{max}	5.300 N	Load capacity dyn.
$C_{0 max}$	4.950 N	Load capacity stat.
$\approx m$	0,19 kg	Weight

Mounting dimensions

J_{L4}	9 mm
N_2	2,5 mm

