



KH50-PP [↗](#)

Linear Ball Bearing

Linear ball bearings with initial greasing,
sealed on both sides, with relubrication facility

Technical information

Your current product variant

Size code	50	
Seal	PP	Sealed

Main Dimensions & Performance Data

F_w	50 mm	Diameter shaft
D	62 mm	Outer diameter
L	70 mm	Length
C_{min}	6.800 N	Load capacity dyn.
$C_{0 min}$	6.300 N	Load capacity stat.
C_{max}	6.800 N	Load capacity dyn.
$C_{0 max}$	7.000 N	Load capacity stat.
$\approx m$	255 g	Weight

Mounting dimensions

J_{L4}	9 mm
N_2	2,5 mm

