
**LFR50/5-4-2Z-HLC**

Yoke type track roller

Yoke type track roller

Technical information



Your current product variant

Size code	50/5	
Seal	2Z	Gap seal on both sides
Code	HLC	

Main Dimensions & Performance Data

d	5 mm	
D _{max}	16 mm	
B	8 mm	Width, inner ring
≈m	7,2 g	Weight

Mounting dimensions

A _T	9 mm	
C	7 mm	
D _a	14,54 mm	Diameter of rolling
d _s	4 mm	
r _{min}	0,2 mm	

Main dimensions

C _{r w}	1.560 N	Effective dynamic load rating as track roller (radial)
C _{0r w}	850 N	Effective static load rating as track roller (radial)
C _{ur w}	43 N	Limit of fatigue load
F _{r per}	1.700 N	Permissible dynamic limit load
F _{0r per}	1.700 N	Permissible static limit load



Additional information

LFE/LFZ	siehe Katalog: LF1	Possible roller-pin combination
---------	--------------------	---------------------------------