


KGB16-PP-AS

Linear Ball Bearing and Housing Unit

Linear ball bearing and housing unit; sealed, greased, with relubrication facility; corrosion-resistant design possible

Technical information



Your current product variant

Size code	16
Seal	PP
Relubrication	AS

Technical data

	5	Ball rows
≈m	0,14 kg	Weight

Main Dimensions & Performance Data

F _W	16 mm	Diameter of ball complement
Tol F _W	+ 0,009 mm	Upper tolerance
Tol F _W	- 0,001 mm	Lower tolerance
H	37,5 mm	Height
L	36 mm	Length
Tol L	h12	Tolerance
B	56 mm	Width
C	710 N	Load capacity dyn.
C ₀	530 N	Load capacity stat.



Mounting dimensions

J B	46 mm	
Tol J B	+ 0,15 mm	Upper tolerance
Tol J B	- 0,15 mm	Lower tolerance
B 1	35 mm	
A 5	28 mm	
Tol A 5	+ 0,02 mm	Upper tolerance
Tol A 5	- 0,02 mm	Lower tolerance
L 4	15 mm	
L 5	22 mm	Length of Shaft Support Block without drive System
J L 4	11 mm	Distance
H 2	20 mm	Center height
Tol H 2	+ 0,015 mm	Upper tolerance
Tol H 2	- 0,015 mm	Lower tolerance
A 3	15 mm	
H 6	6 mm	
N 1	5,5 mm	
N 3	10 mm	
K 5	M5	
K 8	NIPA1	Lubrication nipple