

**KGB012-PP-AS** **Linear Ball Bearing and Housing Unit**

Linear ball bearing and housing unit; open design, sealed, greased, with relubrication facility; corrosion-resistant design possible

Technical information**Your current product variant**

Size code	12
Seal	PP
Relubrication feature	AS

Technical data

	4	Ball rows
≈m	84,7 g	Weight

Main Dimensions & Performance Data

F _W	12 mm	Diameter of ball complement
H	32 mm	Center height
L	32 mm	Length
Tol L	h12	Tolerance
B	52 mm	Width
C	600 N	Load capacity dyn.
C ₀	445 N	Load capacity stat. C ₀



Mounting dimensions

J _B	42 mm	
Tol J _B	+ 0,15 mm	Upper tolerance
Tol J _B	- 0,15 mm	Lower tolerance
B ₁	31,6 mm	
A ₅	26 mm	
Tol A ₅	+ 0,02 mm	Upper tolerance
Tol A ₅	- 0,02 mm	Lower tolerance
B ₂	7,7 mm	
L ₄	12 mm	Distance
L ₅	20 mm	Distance
J L ₄	6,5 mm	Distance
H ₂	20 mm	Height shaft
Tol H ₂	+ 0,015 mm	Upper tolerance
Tol H ₂	- 0,015 mm	Lower tolerance
A ₃	15 mm	
H ₆	6 mm	
N ₁	5,5 mm	
N ₃	10 mm	
K ₅	M5	
K ₈	NIPA1	Lubrication nipple
α	78 °	Angle