


KGBA50-PP-AS

Linear Ball Bearing and Housing Unit

Linear ball bearing and housing unit; sealed, greased, with relubrication facility; corrosion-resistant design possible

Technical information



Your current product variant

Size code	50
Seal	PP
Relubrication feature	AS

Technical data

6 Ball rows

≈m 1,88 kg Weight

Main Dimensions & Performance Data

F _W	50 mm	Diameter of ball complement
Tol F _W	+ 0,013 mm	Upper tolerance
Tol F _W	- 0,002 mm	Lower tolerance
H	98 mm	Height
L	100 mm	Length
Tol L	h12	Tolerance
B	130 mm	Width
C	8.700 N	Load capacity dyn. C
C ₀	6.300 N	Load capacity stat. C0



Mounting dimensions

J _B	108 mm	
Tol J _B	+ 0,2 mm	Upper tolerance
Tol J _B	- 0,2 mm	Lower tolerance
A ₅	65 mm	
Tol A ₅	+ 0,015 mm	Upper tolerance
Tol A ₅	- 0,015 mm	Lower tolerance
L ₄	70 mm	
L ₅	72 mm	
J _L	50 mm	
Tol J _L	+ 0,2 mm	Upper tolerance
Tol J _L	- 0,2 mm	Lower tolerance
H ₂	50 mm	Center Height
Tol H ₂	+ 0,015 mm	Upper tolerance
Tol H ₂	- 0,015 mm	Lower tolerance
A ₃	34 mm	
H ₆	12,5 mm	
Tol H ₆	- 0,5 mm	Tolerance
N ₁	9,2 mm	
N ₃	15 mm	
K ₅	M8	
K ₈	NIPA2	Lubrication nipple