


KGBAS30-PP-AS

Linear Ball Bearing and Housing Unit

Linear ball bearing and housing unit; sealed, greased, with relubrication facility; corrosion-resistant design possible

Technical information



Your current product variant

Size code	30
Seal	PP
Relubrication	AS

Technical data

	6	Ball rows
≈m	0,61 kg	Weight

Main Dimensions & Performance Data

F _W	30 mm	Diameter of ball complement
H	67 mm	Height
L	68 mm	Length
Tol L	h12	Tolerance
B	84 mm	Width
C	3.600 N	Load capacity dyn. C
C ₀	2.850 N	Load capacity stat. C ₀



Mounting dimensions

J _B	68 mm	
Tol J _B	+ 0,2 mm	Upper tolerance
Tol J _B	- 0,2 mm	Lower tolerance
A ₅	42 mm	
Tol A ₅	+ 0,01 mm	Upper tolerance
Tol A ₅	- 0,01 mm	Lower tolerance
L ₄	60 mm	
L ₅	48 mm	
J _L	45 mm	
Tol J _L	- 0,2 mm	Upper tolerance
Tol J _L	- 0,2 mm	Lower tolerance
H ₂	35 mm	Center Height
Tol H ₂	+ 0,01 mm	Upper tolerance
Tol H ₂	- 0,01 mm	Lower tolerance
A ₃	25 mm	
H ₆	8,7 mm	
Tol H ₆	- 0,5 mm	Tolerance
N ₁	6,8 mm	
N ₃	11 mm	
K ₅	M6	
K ₈	NIPA2	Lubrication nipple
W	10 mm	Width across flats