



**FAG****6004-C-2HRS-C3>V** [↗](#)

## Deep groove ball bearing

Deep groove ball bearing 60...-C-2HRS, single row, Generation C, seals, steel sheet metal cage

## Technical information



## Your current product variant

|                                  |              |                                         |
|----------------------------------|--------------|-----------------------------------------|
| Version code                     | >V           | Not marked on bearing                   |
| Changed internal design          | C            | GenerationC                             |
| Type of Seal                     | 2HRS         | Contact seal on both sides              |
| Cage                             | JN           | Steel sheet metal                       |
| Tolerance class                  | P6           | Class 6 (ISO 492:2023)                  |
| Dimensional / heat stabilization | SN           | Rings dimensional stabilized up to 120° |
| Lubricant                        | GA14         | Ball bearing grease, low noise          |
| Radial internal clearance        | C3 (Group 3) | Internal clearance larger than CN       |
| Bore type                        | Z            | Cylindrical                             |

## Main Dimensions &amp; Performance Data

|                 |              |                                   |
|-----------------|--------------|-----------------------------------|
| d               | 20 mm        | Bore diameter                     |
| D               | 42 mm        | Outside diameter                  |
| B               | 12 mm        | Width                             |
| C <sub>r</sub>  | 10.600 N     | Basic dynamic load rating, radial |
| C <sub>0r</sub> | 5.000 N      | Basic static load rating, radial  |
| C <sub>ur</sub> | 340 N        | Fatigue load limit, radial        |
| n <sub>G</sub>  | 15.300 1/min | Limiting speed                    |
| ≈m              | 0,065 kg     | Weight                            |



Mounting dimensions

|              |         |                                      |
|--------------|---------|--------------------------------------|
| $d_{a\ min}$ | 23,2 mm | Minimum diameter shaft shoulder      |
| $D_{a\ max}$ | 38,8 mm | Maximum diameter of housing shoulder |
| $r_{a\ max}$ | 0,6 mm  | Maximum fillet radius                |

Dimensions

|            |          |                              |
|------------|----------|------------------------------|
| $r_{\min}$ | 0,6 mm   | Minimum chamfer dimension    |
| $D_1$      | 35,45 mm | Shoulder diameter outer ring |
| $D_2$      | 37,38 mm | Caliber diameter outer ring  |
| $d_1$      | 26,55 mm | Shoulder diameter inner ring |
| $d_2$      | 25,38 mm | Caliber diameter inner ring  |

Temperature range

|            |        |                            |
|------------|--------|----------------------------|
| $T_{\min}$ | -20 °C | Operating temperature min. |
| $T_{\max}$ | 100 °C | Operating temperature max. |

Calculation factors

|       |      |                    |
|-------|------|--------------------|
| $f_0$ | 13,8 | Calculation factor |
|-------|------|--------------------|

Characteristics

|                                                                                     |                                                |
|-------------------------------------------------------------------------------------|------------------------------------------------|
|  | Radial load                                    |
|  | Axial load in one direction                    |
|  | Axial load in two directions                   |
|  | Lifetime lubrication, freedom from maintenance |
|  | Grease Lubrication                             |
|  | Sealed on both sides                           |