



**FAG****6004-C-C3>V** [🔗](#)

Deep groove ball bearing

Deep groove ball bearing 60...-C, single row,
Generation C, steel sheet metal cage

Technical information



Your current product variant

Changed internal design	C	GenerationC
Sealing	Without	Not sealed
Cage	JN	Steel sheet metal
Tolerance class	P6	Class 6 (ISO 492:2023)
Dimensional / heat stabilization	SN	Rings dimensional stabilized up to 120°
Lubricant	Without	Bearing not greased
Radial internal clearance	C3 (Group 3)	Internal clearance larger than CN
Bore type	Z	Cylindrical
Version code	>V	Not marked on bearing

Main Dimensions & Performance Data

d	20 mm	Bore diameter
D	42 mm	Outside diameter
B	12 mm	Width
C _r	10.600 N	Basic dynamic load rating, radial
C _{0r}	5.000 N	Basic static load rating, radial
C _{ur}	340 N	Fatigue load limit, radial
n _G	27.500 1/min	Limiting speed
n _{gr}	19.700 1/min	Reference speed
≈m	0,061 kg	Weight



Mounting dimensions

$d_{a\ min}$	23,2 mm	Minimum diameter shaft shoulder
$D_{a\ max}$	38,8 mm	Maximum diameter of housing shoulder
$r_{a\ max}$	0,6 mm	Maximum fillet radius

Dimensions

$r_{\ min}$	0,6 mm	Minimum chamfer dimension
$D_{\ 1}$	35,45 mm	Shoulder diameter outer ring
$D_{\ 2}$	37,38 mm	Caliber diameter outer ring
$d_{\ 1}$	26,55 mm	Shoulder diameter inner ring
$d_{\ 2}$	25,38 mm	Caliber diameter inner ring

Temperature range

$T_{\ min}$	-30 °C	Operating temperature min.
$T_{\ max}$	120 °C	Operating temperature max.

Calculation factors

$f_{\ 0}$	13,8	Calculation factor
-----------	------	--------------------

Characteristics

	Radial load
	Axial load in one direction
	Axial load in two directions
	Grease Lubrication
	Oil Lubrication
	Not sealed