



**FAG****6201-C-C3>V**

Deep groove ball bearing

Deep groove ball bearing 62...-C, single row,
Generation C, steel sheet metal cage

Technical information



Your current product variant

Version code	>V	Not marked on bearing
Changed internal design	C	GenerationC
Type of Seal	Without	Not sealed
Cage	JN	Steel sheet metal
Tolerance class	P6	Class 6 (ISO 492:2023)
Dimensional / heat stabilization	SN	Rings dimensional stabilized up to 120°
Lubricant	Without	Bearing not greased
Radial internal clearance	C3 (Group 3)	Internal clearance larger than CN
Bore type	Z	Cylindrical

Main Dimensions & Performance Data

d	12 mm	Bore diameter
D	32 mm	Outside diameter
B	10 mm	Width
C _r	8.000 N	Basic dynamic load rating, radial
C _{0r}	3.100 N	Basic static load rating, radial
C _{ur}	213 N	Fatigue load limit, radial
n _G	37.000 1/min	Limiting speed
n _{gr}	24.600 1/min	Reference speed
≈m	0,033 kg	Weight



Mounting dimensions

$d_{a\ min}$	16,2 mm	Minimum diameter shaft shoulder
$D_{a\ max}$	27,8 mm	Maximum diameter of housing shoulder
$r_{a\ max}$	0,6 mm	Maximum fillet radius

Dimensions

$r_{\ min}$	0,6 mm	Minimum chamfer dimension
D_1	26 mm	Shoulder diameter outer ring
D_2	27,92 mm	Caliber diameter outer ring
d_1	18,31 mm	Shoulder diameter inner ring
d_2	17,34 mm	Caliber diameter inner ring

Temperature range

$T_{\ min}$	-30 °C	Operating temperature min.
$T_{\ max}$	120 °C	Operating temperature max.

Calculation factors

f_0	12,3	Calculation factor
-------	------	--------------------

Characteristics

	Radial load
	Axial load in one direction
	Axial load in two directions
	Grease Lubrication
	Oil Lubrication
	Not sealed