




FAG

30208-H

Tapered roller bearing

Tapered roller bearings 302, main dimensions
acc. to DIN 720, separable

Technical information



Your current product variant

Tolerance class	PN	Normal (ISO 492:2023)
Heat treatment	Standard	
Cage	Standard	Sheet steel cage, window cage, roller-guided
Internal design	Standard	
Quality level	H	
Number of rows	1	Single-row design

Main Dimensions & Performance Data

d	40 mm	Bore diameter
D	80 mm	Outside diameter
B	18 mm	Width, inner ring
C	16 mm	Width, outer ring
T	19,75 mm	Width, total
C _r	58.000 N	Basic dynamic load rating, radial
C _{0r}	67.000 N	Basic static load rating, radial
C _{ur}	7.800 N	Fatigue load limit, radial
n _G	7.680 1/min	Limiting speed
n _{gr}	5.900 1/min	Thermal speed rating
≈m	0,435 kg	Weight



Mounting dimensions

$d_{a \max}$	49 mm	Maximum diameter of shaft shoulder
$d_{b \min}$	47 mm	Minimum diameter of shaft shoulder
$D_{a \min}$	69 mm	Minimum diameter of housing shoulder
$D_{a \max}$	73 mm	Maximum diameter of housing shoulder
$D_{b \min}$	74 mm	Minimum diameter of housing shoulder
$C_{a \min}$	3 mm	Minimum axial space
$C_{b \min}$	3,5 mm	Minimum axial space
$r_{a \max}$	1,5 mm	Maximum fillet radius of shaft
$r_{b \max}$	1,5 mm	Maximum fillet radius of housing

Dimensions

$r_{1, 2 \min}$	1,5 mm	Minimum chamfer dimension of inner ring back face
$r_{3, 4 \min}$	1,5 mm	Minimum chamfer dimension of outer ring back face
a	17 mm	Distance between the apexes of the pressure cones
$d_1 \max$	59,9 mm	Maximum guidance rib diameter of inner ring

Temperature range

$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	120 °C	Operating temperature max.

Calculation factors

e	0,37	Limiting value of F_a/F_r for the applicability of diff. Values of factors X and Y
Y	1,6	Dynamic axial load factor
Y_0	0,88	Static axial load factor

Additional information

T3DB040

Comparative designation to ISO 10317 and ISO 355



Characteristics

-  Radial load
-  Axial load in one direction
-  Grease Lubrication
-  Oil Lubrication
-  Not sealed