


**FAG****6305-H-2Z>N**

Deep groove ball bearing

Deep groove ball bearing 63...-H-2Z, single row, H-Series, shields, steel sheet metal cage

Technical information



Your current product variant

Version code	>N	Not marked on bearing
Changed internal design	H	Design variant H (H-Series)
Type of Seal	2Z	Non-contact shield on both sides
Cage	JN	Steel sheet metal
Tolerance class	PN	Normal (ISO 492:2023)
Dimensional / heat stabilization	SN	Rings dimensional stabilized up to 120°
Lubricant	Lubricating grease	
Radial internal clearance	CN (Group N)	Normal internal clearance
Bore type	Z	Cylindrical

Main Dimensions & Performance Data

d	25 mm	Bore diameter
D	62 mm	Outside diameter
B	17 mm	Width
C _r	22.410 N	Basic dynamic load rating, radial
C _{0r}	11.510 N	Basic static load rating, radial
C _{ur}	710 N	Fatigue load limit, radial
n _G	13.700 1/min	Limiting speed
n _{gr}	12.300 1/min	Reference speed
≈m	0,22 kg	Weight



Mounting dimensions

$d_{a\min}$	32 mm	Minimum diameter shaft shoulder
$D_{a\max}$	55 mm	Maximum diameter of housing shoulder
$r_{a\max}$	1 mm	Maximum fillet radius

Dimensions

$r_{\min}$	1,1 mm	Minimum chamfer dimension
D_1	51 mm	Shoulder diameter outer ring
D_2	53 mm	Caliber diameter outer ring
d_1	36 mm	Shoulder diameter inner ring
d_2	33,8 mm	Caliber diameter inner ring

Temperature range

$T_{\min}$	-20 °C	Operating temperature min.
$T_{\max}$	120 °C	Operating temperature max.

Calculation factors

f_0	12,4	Calculation factor
-------	------	--------------------

Characteristics

	Radial load
	Axial load in one direction
	Axial load in two directions
	Lifetime lubrication, freedom from maintenance
	Grease Lubrication
	Sealed on both sides