




FAG

30212-H

Tapered roller bearing

Tapered roller bearings 302, main dimensions
acc. to DIN 720, separable

Technical information



Your current product variant

Tolerance class	PN	Normal (ISO 492:2023)
Heat treatment	Standard	
Cage	Standard	Sheet steel cage, window cage, roller-guided
Internal design	Standard	
Quality level	H	
Number of rows	1	Single-row design

Main Dimensions & Performance Data

d	60 mm	Bore diameter
D	110 mm	Outside diameter
B	22 mm	Width, inner ring
C	19 mm	Width, outer ring
T	23,75 mm	Width, total
C _r	96.900 N	Basic dynamic load rating, radial
C _{0r}	121.000 N	Basic static load rating, radial
C _{ur}	14.300 N	Fatigue load limit, radial
n _G	5.440 1/min	Limiting speed
n _{gr}	4.300 1/min	Thermal speed rating
≈m	0,92 kg	Weight



Mounting dimensions

d _a max	70 mm	Maximum diameter of shaft shoulder
d _b min	69 mm	Minimum diameter of shaft shoulder
D _a min	96 mm	Minimum diameter of housing shoulder
D _a max	101 mm	Maximum diameter of housing shoulder
D _b min	103 mm	Minimum diameter of housing shoulder
C _a min	4 mm	Minimum axial space
C _b min	4,5 mm	Minimum axial space
r _a max	2 mm	Maximum fillet radius of shaft
r _b max	1,5 mm	Maximum fillet radius of housing

Dimensions

r _{1, 2} min	2 mm	Minimum chamfer dimension of inner ring back face
r _{3, 4} min	1,5 mm	Minimum chamfer dimension of outer ring back face
a	22 mm	Distance between the apexes of the pressure cones
d ₁ max	84,4 mm	Maximum guidance rib diameter of inner ring

Temperature range

T _{min}	-30 °C	Operating temperature min.
T _{max}	120 °C	Operating temperature max.

Calculation factors

e	0,41	Limiting value of Fa/Fr for the applicability of diff. Values of factors X and Y
Y	1,48	Dynamic axial load factor
Y ₀	0,81	Static axial load factor

Additional information

T3EB060	Comparative designation to ISO 10317 and ISO 355
---------	--



Characteristics

-  Radial load
-  Axial load in one direction
-  Grease Lubrication
-  Oil Lubrication
-  Not sealed