



**FAG****6009-H-2RSR-C3>N**

Deep groove ball bearing

Deep groove ball bearing 60...-H-2RSR, single row, H-Series, seals, steel sheet metal cage

Technical information



Your current product variant

Version code	>N	Not marked on bearing
Changed internal design	H	Design variant H (H-Series)
Type of Seal	2RSR	Contact seal on both sides
Cage	JN	Steel sheet metal
Tolerance class	PN	Normal (ISO 492:2023)
Dimensional / heat stabilization	SN	Rings dimensional stabilized up to 120°
Lubricant	Lubricating grease	
Radial internal clearance	C3 (Group 3)	Internal clearance larger than CN
Bore type	Z	Cylindrical

Main Dimensions & Performance Data

d	45 mm	Bore diameter
D	75 mm	Outside diameter
B	16 mm	Width
C _r	19.890 N	Basic dynamic load rating, radial
C _{0r}	13.990 N	Basic static load rating, radial
C _{ur}	830 N	Fatigue load limit, radial
n _G	4.900 1/min	Limiting speed
≈m	0,242 kg	Weight



Mounting dimensions

$d_{a\min}$	49,6 mm	Minimum diameter shaft shoulder
$D_{a\max}$	70,4 mm	Maximum diameter of housing shoulder
$r_{a\max}$	1 mm	Maximum fillet radius

Dimensions

$r_{\min}$	1 mm	Minimum chamfer dimension
D_1	65,8 mm	Shoulder diameter outer ring
D_2	68,7 mm	Caliber diameter outer ring
d_1	54,3 mm	Shoulder diameter inner ring

Temperature range

$T_{\min}$	-20 °C	Operating temperature min.
$T_{\max}$	100 °C	Operating temperature max.

Calculation factors

f_0	15,3	Calculation factor
-------	------	--------------------

Characteristics

	Radial load
	Axial load in one direction
	Axial load in two directions
	Lifetime lubrication, freedom from maintenance
	Grease Lubrication
	Sealed on both sides