



**FAG****6311-C-2HRS-C3**

Deep groove ball bearing

Deep groove ball bearing 63...C-2HRS, single row, Generation C, seals, steel sheet metal cage

Technical information



Your current product variant

Changed internal design	C	GenerationC
Type of Seal	2HRS	Contact seal on both sides
Cage	JN	Steel sheet metal
Tolerance class	P6	Class 6 (ISO 492:2023)
Dimensional / heat stabilization	S0	Rings dimensional stabilized up to 150°
Lubricant	GA13	Ball bearing and insert bearing grease
Radial internal clearance	C3 (Group 3)	Internal clearance larger than CN
Bore type	Z	Cylindrical

Main Dimensions & Performance Data

d	55 mm	Bore diameter
D	120 mm	Outside diameter
B	29 mm	Width
C _r	83.000 N	Basic dynamic load rating, radial
C _{0r}	47.500 N	Basic static load rating, radial
C _{ur}	3.300 N	Fatigue load limit, radial
n _G	5.300 1/min	Limiting speed
≈m	1,35 kg	Weight



Mounting dimensions

$d_{a\ min}$	66 mm	Minimum diameter shaft shoulder
$D_{a\ max}$	109 mm	Maximum diameter of housing shoulder
$r_{a\ max}$	2 mm	Maximum fillet radius

Dimensions

$r_{\ min}$	2 mm	Minimum chamfer dimension
D_1	102,15 mm	Shoulder diameter outer ring
D_2	105,3 mm	Caliber diameter outer ring
d_1	74,7 mm	Shoulder diameter inner ring
d_2	72,54 mm	Caliber diameter inner ring

Temperature range

$T_{\ min}$	-20 °C	Operating temperature min.
$T_{\ max}$	100 °C	Operating temperature max.

Calculation factors

f_0	12,9	Calculation factor
-------	------	--------------------

Characteristics

	Radial load
	Axial load in one direction
	Axial load in two directions
	Lifetime lubrication, freedom from maintenance
	Grease Lubrication
	Sealed on both sides