




FAG

16011-A

Deep groove ball bearing

Deep groove ball bearing 160..-A, single row, steel sheet metal cage

Technical information



Your current product variant

Changed internal design	A	Design variant A
Sealing	Without	Not sealed
Cage	JN	Steel sheet metal
Tolerance class	PN	Normal (ISO 492:2023)
Dimensional / heat stabilization	SN	Rings dimensional stabilized up to 120°
Lubricant	Without	Bearing not greased
Radial internal clearance	CN (Group N)	Normal internal clearance
Bore type	Z	Cylindrical

Main Dimensions & Performance Data

d	55 mm	Bore diameter
D	90 mm	Outside diameter
B	11 mm	Width
C _r	20.600 N	Basic dynamic load rating, radial
C _{0r}	16.300 N	Basic static load rating, radial
C _{ur}	940 N	Fatigue load limit, radial
n _G	10.900 1/min	Limiting speed
n _{gr}	6.000 1/min	Reference speed
m	0,259 kg	Weight



Mounting dimensions

$d_{a\min}$	58,2 mm	Minimum diameter shaft shoulder
$D_{a\max}$	86,8 mm	Maximum diameter of housing shoulder
$r_{a\max}$	0,6 mm	Maximum fillet radius

Dimensions

$r_{\min}$	0,6 mm	Minimum chamfer dimension
D_1	78,61 mm	Shoulder diameter outer ring
d_1	69,6 mm	Shoulder diameter inner ring

Temperature range

$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	120 °C	Operating temperature max.

Calculation factors

f_0	16,2	Calculation factor
-------	------	--------------------

Characteristics

	Radial load
	Axial load in one direction
	Axial load in two directions
	Grease Lubrication
	Oil Lubrication
	Not sealed