

**FAG****62304-A-2RSR**

Deep groove ball bearing

Deep groove ball bearing 623..-A-2RSR,
single row, steel sheet metal cage

Technical information



Your current product variant

Changed internal design	A	Design variant A
Type of Seal	2RSR	Contact seal on both sides
Cage	JN	Steel sheet metal
Tolerance class	PN	Normal (ISO 492:2023)
Dimensional / heat stabilization	SN	Rings dimensional stabilized up to 120°
Lubricant	Lubricating grease	
Radial internal clearance	CN (Group N)	Normal internal clearance
Bore type	Z	Cylindrical

Main Dimensions & Performance Data

d	20 mm	Bore diameter
D	52 mm	Outside diameter
B	21 mm	Width
C _r	16.900 N	Basic dynamic load rating, radial
C _{0r}	7.900 N	Basic static load rating, radial
C _{ur}	560 N	Fatigue load limit, radial
n _G	8.900 1/min	Limiting speed
≈m	0,2 kg	Weight



Mounting dimensions

$d_{a\min}$	27 mm	Minimum diameter shaft shoulder
$D_{a\max}$	45 mm	Maximum diameter of housing shoulder
$r_{a\max}$	1 mm	Maximum fillet radius

Dimensions

$r_{\min}$	1,1 mm	Minimum chamfer dimension
D_1	42,2 mm	Shoulder diameter outer ring
D_2	45,1 mm	Caliber diameter outer ring
d_1	30 mm	Shoulder diameter inner ring

Temperature range

$T_{\min}$	-20 °C	Operating temperature min.
$T_{\max}$	100 °C	Operating temperature max.

Calculation factors

f_0	12,4	Calculation factor
-------	------	--------------------

Characteristics

	Radial load
	Axial load in one direction
	Axial load in two directions
	Lifetime lubrication, freedom from maintenance
	Grease Lubrication
	Sealed on both sides