



**FAG****627-2Z-HLN**

Deep groove ball bearing

Deep groove ball bearing 62...-2Z, single row, shields, steel sheet metal cage

Technical information



Your current product variant

Logistical code	HLN	-
Type of Seal	2Z	Non-contact shield on both sides
Cage	JN	Steel sheet metal
Tolerance class	PN	Normal (ISO 492:2023)
Dimensional / heat stabilization	SN	Rings dimensional stabilized up to 120°
Lubricant	Lubricating grease	
Radial internal clearance	CN (Group N)	Normal internal clearance
Bore type	Z	Cylindrical

Main Dimensions & Performance Data

d	7 mm	Bore diameter
D	22 mm	Outside diameter
B	7 mm	Width
C _r	3.500 N	Basic dynamic load rating, radial
C _{0r}	1.370 N	Basic static load rating, radial
C _{ur}	85 N	Fatigue load limit, radial
n _G	40.000 1/min	Limiting speed
n _{gr}	28.000 1/min	Reference speed
≈m	0,014 kg	Weight



Mounting dimensions

$d_{a\ min}$	9,4 mm	Minimum diameter shaft shoulder
$D_{a\ max}$	19,6 mm	Maximum diameter of housing shoulder
$r_{a\ max}$	0,3 mm	Maximum fillet radius

Dimensions

$r_{\ min}$	0,3 mm	Minimum chamfer dimension
D_1	18 mm	Shoulder diameter outer ring
D_2	19,3 mm	Caliber diameter outer ring
d_1	12,3 mm	Shoulder diameter inner ring
d_2	11 mm	Caliber diameter inner ring

Temperature range

$T_{\ min}$	-30 °C	Operating temperature min.
$T_{\ max}$	120 °C	Operating temperature max.

Calculation factors

f_0	12,4	Calculation factor
-------	------	--------------------

Characteristics

	Radial load
	Axial load in one direction
	Axial load in two directions
	Lifetime lubrication, freedom from maintenance
	Grease Lubrication
	Sealed on both sides