



**FAG****63005-A-2RSR**

Deep groove ball bearing

Deep groove ball bearing 630..-A-2RSR,
single row, seals, steel sheet metal cage

Technical information



Your current product variant

Changed internal design	A	Design variant A
Type of Seal	2RSR	Contact seal on both sides
Cage	JN	Steel sheet metal
Tolerance class	PN	Normal (ISO 492:2023)
Dimensional / heat stabilization	SN	Rings dimensional stabilized up to 120°
Lubricant	Lubricating grease	
Radial internal clearance	CN (Group N)	Normal internal clearance
Bore type	Z	Cylindrical

Main Dimensions & Performance Data

d	25 mm	Bore diameter
D	47 mm	Outside diameter
B	16 mm	Width
C _r	10.400 N	Basic dynamic load rating, radial
C _{0r}	5.800 N	Basic static load rating, radial
C _{ur}	365 N	Fatigue load limit, radial
n _G	8.500 1/min	Limiting speed
≈m	0,102 kg	Weight



Mounting dimensions

$d_{a\ min}$	28,2 mm	Minimum diameter shaft shoulder
$D_{a\ max}$	43,8 mm	Maximum diameter of housing shoulder
$r_{a\ max}$	0,6 mm	Maximum fillet radius

Dimensions

$r_{\ min}$	0,6 mm	Minimum chamfer dimension
D_1	40,14 mm	Shoulder diameter outer ring
D_2	42,8 mm	Caliber diameter outer ring
d_1	31,56 mm	Shoulder diameter inner ring

Temperature range

$T_{\ min}$	-20 °C	Operating temperature min.
$T_{\ max}$	100 °C	Operating temperature max.

Calculation factors

f_0	14,4	Calculation factor
-------	------	--------------------

Characteristics

	Radial load
	Axial load in one direction
	Axial load in two directions
	Lifetime lubrication, freedom from maintenance
	Grease Lubrication
	Sealed on both sides