



**FAG****63007-A-2RSR**

Deep groove ball bearing

Deep groove ball bearing 630..-A-2RSR,
single row, seals, steel sheet metal cage

Technical information



Your current product variant

Changed internal design	A	Design variant A
Type of Seal	2RSR	Contact seal on both sides
Cage	JN	Steel sheet metal
Tolerance class	PN	Normal (ISO 492:2023)
Dimensional / heat stabilization	SN	Rings dimensional stabilized up to 120°
Lubricant	Lubricating grease	
Radial internal clearance	CN (Group N)	Normal internal clearance
Bore type	Z	Cylindrical

Main Dimensions & Performance Data

d	35 mm	Bore diameter
D	62 mm	Outside diameter
B	20 mm	Width
C _r	17.000 N	Basic dynamic load rating, radial
C _{0r}	10.300 N	Basic static load rating, radial
C _{ur}	690 N	Fatigue load limit, radial
n _G	6.100 1/min	Limiting speed
≈m	0,212 kg	Weight



Mounting dimensions

$d_{a\min}$	39,6 mm	Minimum diameter shaft shoulder
$D_{a\max}$	57,4 mm	Maximum diameter of housing shoulder
$r_{a\max}$	1 mm	Maximum fillet radius

Dimensions

$r_{\min}$	1 mm	Minimum chamfer dimension
D_1	53,63 mm	Shoulder diameter outer ring
D_2	56,03 mm	Caliber diameter outer ring
d_1	43,5 mm	Shoulder diameter inner ring

Temperature range

$T_{\min}$	-20 °C	Operating temperature min.
$T_{\max}$	100 °C	Operating temperature max.

Calculation factors

f_0	14,9	Calculation factor
-------	------	--------------------

Characteristics

	Radial load
	Axial load in one direction
	Axial load in two directions
	Lifetime lubrication, freedom from maintenance
	Grease Lubrication
	Sealed on both sides