

**FAG****4202-BB-TVH**

Deep groove ball bearing

Deep groove ball bearing 42...-BB-TVH,
double row, plastic cage

Technical information



Your current product variant

Design variant	B	Bearing without filling slot
Tolerance class	PN	Normal (ISO 492:2023)
Changed internal design	B	B
Cage	TVH	Solid cage made of glass-fiber reinforced polyamid PA66
Lubricant	GA14	Ball bearing grease, low noise
Dimensional / heat stabilization	SN	Rings dimensional stabilized up to 120°
Radial internal clearance	CN (Group N)	Normal internal clearance

Main Dimensions & Performance Data

d	15 mm	Bore diameter
D	35 mm	Outside diameter
B	14 mm	Width
C _r	12.400 N	Basic dynamic load rating, radial
C _{0r}	7.400 N	Basic static load rating, radial
C _{ur}	385 N	Fatigue load limit, radial
n _G	20.100 1/min	Limiting speed
n _{gr}	16.400 1/min	Reference speed
≈m	0,059 kg	Weight



Mounting dimensions

$d_{a\min}$	19,2 mm	Minimum diameter shaft shoulder
$D_{a\max}$	30,8 mm	Maximum diameter of housing shoulder
$r_{a\max}$	0,6 mm	Maximum fillet radius

Dimensions

$r_{\min}$	0,6 mm	Minimum chamfer dimension
D_1	28,95 mm	Shoulder diameter outer ring
d_1	21,4 mm	Shoulder diameter inner ring

Temperature range

$T_{\min}$	-20 °C	Operating temperature min.
$T_{\max}$	120 °C	Operating temperature max.

Calculation factors

f_0	13,1	Calculation factor
-------	------	--------------------

Characteristics

	Radial load
	Axial load in one direction
	Axial load in two directions
	Grease Lubrication
	Not sealed