

**FAG****4210-BB-TVH**

Deep groove ball bearing

Deep groove ball bearing 42...-BB-TVH,
double row, plastic cage

Technical information



Your current product variant

Design variant	B	Bearing without filling slot
Tolerance class	PN	Normal (ISO 492:2023)
Changed internal design	B	B
Cage	TVH	Solid cage made of glass-fiber reinforced polyamid PA66
Lubricant	GA13	Ball bearing and insert bearing grease
Dimensional / heat stabilization	SN	Rings dimensional stabilized up to 120°
Radial internal clearance	CN (Group N)	Normal internal clearance

Main Dimensions & Performance Data

d	50 mm	Bore diameter
D	90 mm	Outside diameter
B	23 mm	Width
C _r	46.500 N	Basic dynamic load rating, radial
C _{0r}	42.000 N	Basic static load rating, radial
C _{ur}	2.200 N	Fatigue load limit, radial
n _G	7.400 1/min	Limiting speed
n _{gr}	6.300 1/min	Reference speed
≈m	0,582 kg	Weight



Mounting dimensions

$d_{a\min}$	57 mm	Minimum diameter shaft shoulder
$D_{a\max}$	83 mm	Maximum diameter of housing shoulder
$r_{a\max}$	1 mm	Maximum fillet radius

Dimensions

$r_{\min}$	1,1 mm	Minimum chamfer dimension
D_1	77,12 mm	Shoulder diameter outer ring
d_1	62,8 mm	Shoulder diameter inner ring

Temperature range

$T_{\min}$	-20 °C	Operating temperature min.
$T_{\max}$	120 °C	Operating temperature max.

Calculation factors

f_0	15,2	Calculation factor
-------	------	--------------------

Characteristics

-  Radial load
-  Axial load in one direction
-  Axial load in two directions
-  Grease Lubrication
-  Not sealed