


**GAY25-XL-NPP-B** **Radial insert ball bearing**

Radial insert ball bearings GAY...NPP-B,
spherical outer ring, location by grub screws,
P seals on both sides

X-life**Technical information****Main Dimensions & Performance Data**

d	25 mm	Bore diameter
D _{SP}	52 mm	Outside diameter
B	27 mm	Width
C _{0r}	7.800 N	Basic static load rating, radial
C _{ur}	410 N	Fatigue load limit, radial
C _r	14.000 N	Basic dynamic load rating, radial
≈m	0,15 kg	Weight

Dimensions

C	15 mm	Width, outer ring
S	7,5 mm	Distance raceway
d ₁	33,5 mm	Rib diameter inner ring
d ₂	30,4 mm	Rib diameter sealing inner ring
C _a	3,9 mm	Distance to lubrication hole
A	5 mm	Distance thread
W	2,5 mm	Width of flats

Temperature range

T _{min}	-20 °C	Operating temperature min.
T _{max}	120 °C	Operating temperature max.



Calculation factors

f_0	13,8	Calculation factor
-------	------	--------------------

Characteristics

-  Radial load
-  Axial load in one direction
-  Axial load in two directions
-  Lifetime lubrication, freedom from maintenance
-  Grease Lubrication
-  Sealed on both sides
-  Static angular error and misalignment