


**FAG****UC206** **Radial insert ball bearing**

Radial insert ball bearings UC, spherical outer ring, location by grub screws, RSR seals on both sides

Technical information**Main Dimensions & Performance Data**

d	30 mm	Bore diameter
D _{SP}	62 mm	Outside diameter
B	38,1 mm	Width
C _{0r}	11.300 N	Basic static load rating, radial
C _{ur}	590 N	Fatigue load limit, radial
C _r	20.700 N	Basic dynamic load rating, radial
≈m	327 g	Weight

Dimensions

C	19 mm	Width, outer ring
C ₂	19,6 mm	Sealing total width
S	15,9 mm	Distance raceway
d ₁	40,2 mm	Rib diameter inner ring
C _a	5 mm	Distance to lubrication hole
A	5 mm	Distance thread
W	3 mm	Width of flats

Temperature range

T _{min}	-20 °C	Operating temperature min.
T _{max}	100 °C	Operating temperature max.



Calculation factors

f_0	13,8	Calculation factor
-------	------	--------------------

Characteristics

-  Radial load
-  Axial load in one direction
-  Axial load in two directions
-  Lifetime lubrication, freedom from maintenance
-  Grease Lubrication
-  Sealed on both sides
-  Static angular error and misalignment