



**FAG****X-life****7004-B-XL-2RS-TVP**

Angular contact ball bearing

Angular contact ball bearing 70..-B-XL-2RS-TVP, single row, X-life, seals, plastic cage

Technical information



Your current product variant

Design variant	B	B
Type of Seal	2RS	Contact seal on both sides
Cage	TVP	Solid cage made of glass-fiber reinforced polyamid PA66
Tolerance class	PN	Normal (ISO 492:2023)
Dimensional / heat stabilization	S0	Rings dimensional stabilized up to 150°
Lubricant	GA14	Ball bearing grease, low noise

Main Dimensions & Performance Data

d	20 mm	Bore diameter
D	42 mm	Outside diameter
B	12 mm	Width
C _r	14.500 N	Basic dynamic load rating, radial
C _{0r}	8.000 N	Basic static load rating, radial
C _{ur}	560 N	Fatigue load limit, radial
n _G	9.800 1/min	Limiting speed
≈m	0,06 kg	Weight



Mounting dimensions

$d_{a\ min}$	23,2 mm	Minimum diameter of shaft shoulder
$D_{a\ max}$	38,8 mm	Maximum diameter of housing shoulder
$D_{b\ max}$	40 mm	Maximum diameter of housing shoulder
$r_{a\ max}$	0,6 mm	Maximum fillet radius of shaft
$r_{a1\ max}$	0,3 mm	Maximum fillet radius of housing

Dimensions

$r_{\min}$	0,6 mm	Minimum chamfer dimension
$r_{1\ min}$	0,3 mm	Minimum chamfer dimension
D_1	34,82 mm	Shoulder diameter on outer ring wide side face
D_2	35,5 mm	Caliber diameter on outer ring wide side face
D_3	39,8 mm	Caliber diameter on outer ring small side face
d_1	28,94 mm	Shoulder diameter on inner ring wide side face
d_2	26,52 mm	Caliber diameter on inner ring wide side face
a	19,4 mm	Distance between the apexes of the pressure cones
α	40 °	Contact angle

Temperature range

$T_{\min}$	-20 °C	Operating temperature min.
$T_{\max}$	100 °C	Operating temperature max.

Characteristics

	Radial load
	Axial load in one direction
	Lifetime lubrication, freedom from maintenance
	Grease Lubrication
	Sealed on both sides