


**FAG****X-life****7006-B-XL-TVP** [🔗](#)

Angular contact ball bearing

Angular contact ball bearing 70..-B-XL-TVP,
single row, X-life, plastic cage

Technical information



Your current product variant

Design variant	B	B
Sealing	Without	Not sealed
Cage	TVP	Solid cage made of glass-fiber reinforced polyamid PA66
Tolerance class	PN	Normal (ISO 492:2023)
Dimensional / heat stabilization	S0	Rings dimensional stabilized up to 150°
Lubricant	Without	Bearing not greased

Main Dimensions & Performance Data

d	30 mm	Bore diameter
D	55 mm	Outside diameter
B	13 mm	Width
C _r	19.900 N	Basic dynamic load rating, radial
C _{0r}	13.400 N	Basic static load rating, radial
C _{ur}	930 N	Fatigue load limit, radial
n _G	16.800 1/min	Limiting speed
n _{gr}	10.200 1/min	Reference speed
≈m	0,106 kg	Weight



Mounting dimensions

$d_{a\ min}$	34,6 mm	Minimum diameter of shaft shoulder
$D_{a\ max}$	50,4 mm	Maximum diameter of housing shoulder
$D_{b\ max}$	51,8 mm	Maximum diameter of housing shoulder
$r_{a\ max}$	1 mm	Maximum fillet radius of shaft
$r_{a1\ max}$	0,6 mm	Maximum fillet radius of housing

Dimensions

$r_{\min}$	1 mm	Minimum chamfer dimension
$r_{1\ min}$	0,6 mm	Minimum chamfer dimension
D_1	47,05 mm	Shoulder diameter on outer ring wide side face
D_2	47,7 mm	Caliber diameter on outer ring wide side face
D_3	51,93 mm	Caliber diameter on outer ring small side face
d_1	41,26 mm	Shoulder diameter on inner ring wide side face
d_2	38,04 mm	Caliber diameter on inner ring wide side face
a	24,9 mm	Distance between the apexes of the pressure cones
α	40 °	Contact angle

Temperature range

$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	120 °C	Operating temperature max.

Characteristics

	Radial load
	Axial load in one direction
	Grease Lubrication
	Oil Lubrication
	Not sealed